

Garant**Screw-on toolholder, right-hand, Shank / insert size: 12/11 mm****Order data**

Order number	260906 12/11
GTIN	4045197805096
Item class	21T

Technical description

Head length L ₁	19 mm
suitable indexable insert	TC.. 1102..
Insert size	11 mm
Shank size	12 mm
ISO code toolholder	STGCR/L 1212F11
Pack of insert screws	269028 18
Overall length L	80 mm
Functional width L ₄	16 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	90 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 18

269028 18

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500