



Solid carbide HPC drill Weldon shank DIN 6535 HB, TiAlN, Ø h7: 5,3 mm



Order data

Order number	122505 5,3
GTIN	4045197391438
Item class	11E

Description

Version:

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**. **Convex cutting edges** with honed edges and special flute profile for **short chips**, even on long chipping materials.

Recommendation:

Maximum drilling depth:

clamping slot length (see table) less 1.5×nominal Ø.

Note:

NEW GENERATION AVAILABLE!

Recommended successor products are No. 122426 and 122436.

Machining strategy: HPC

Norm: DIN 6537 K

Tolerance nominal Ø: h7

Number of cutting edges Z: 2

Tolerance nominal Ø: h7

Flute length: 28 mm

Overall length L_{tot} : 66 mm

Shank Ø: 6 mm

Feed f in steel < 1100 N/mm²: 0.15 mm/rev.

Technical description

Number of cutting edges Z	2
Feed f in steel < 1100 N/mm ²	0.15 mm/rev.
Nominal Ø	5.3 mm
Flute length	28 mm

Shank tolerance	h6
Tolerance nominal Ø	h7
Shank Ø	6 mm
Overall length L _{tot}	66 mm
Norm	DIN 6537 K
recommended maximum drilling depth	20.1 mm
Coating	TiAlN
Tool material	Solid carbide
Drill depth up to	4×D
Point angle	140 degrees
Skaft	DIN 6535 HB to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Colour ring	green