



## Hand-held circular saw, Type: GKT55GCE



### Order data

Order number	078181 GKT55GCE
GTIN	3165140607759
Item class	03B

### Description

#### Version:

Powerful circular saws with

- **Spindle locking.**
- **Constant electronics.**
- **Dust extraction.**
- **Smooth start-up.**
- **Compatible with guide rail (FSN 1600).**

**Plunging circular saw** with powerful 1400 Watt motor.

- **Adjustable speed and Constant-Speed electronics for cutting a range of different materials such as wood, board materials, aluminium and acrylic glass.**
- **Comfortable working especially indoors due to the highly efficient dust extraction and noise-reduced saw blade.**
- **Clean precise cutting due to high-quality machine components, precision saw blade, suitable guide rail system and exact setting of the cutting angle and depth.**

#### Supplied with:

Including circular saw blade (Top Precision Best for Wood dia. 165 mm), L-BOXX 374N, 1/1 L-BOXX inlay, device.

#### Note:

Circular saw blades can be found under 583920.

Packaging: Modular case (L-Boxx)

Manufacturer's designation: GKT 55 GCE

Version: Plunging circular saw

Power consumption: 1400 W  
maximum speed: 6250 min<sup>-1</sup>  
Saw blade Ø: 165 mm  
Saw blade bore Ø: 20 mm

## Technical description

maximum cutting depth 90°	57 mm
Manufacturer's designation	GKT 55 GCE
Weight	4.7 kg
Saw blade bore Ø	20 mm
Power consumption	1400 W
Saw blade Ø	165 mm
maximum vibration to EN	< 2.5 m/s <sup>2</sup>
maximum speed	6250 min <sup>-1</sup>
Version	Plunging circular saw
Power supply	Mains operated
Packaging	Modular case (L-Boxx)
Type of product	Saw

## Accessories

Circular saw blade expert for Aluminium Blade Ø D 165 mm	583920 165
--	------------