



Straight die grinder, Type: 722325



Order data

Order number	077261 722325
GTIN	4014586880648
Item class	03F

Description

Version:

- **Quiet running due to multiple spindle bearings.**
- **Powerful motor with high cutting power.**
- **Due to speed regulation, outstandingly suitable for cutting stainless steel, and also for grinding and polishing work.**
- **4 m H07 industrial cable.**
- **Suitable for grinding points and carbide milling cutters.**
- **Universal straight die grinder for working where access is difficult.**
- **Slim neck for internal grinding.**
- **Exceptionally handy straight die grinder.**
- **Suitable for grinding stainless steel and for light grinding and polishing work.**
- **Narrow grinding head for inaccessible places.**
- **Variable speed enables the use of different tools.**

Supplied with:

Collet Ø 6 mm, 2 chuck wrenches 13 AF and 17 AF.

Attention:

German version. Order free UK adapter plug No. 08 1172_GB.

Note:

Straight die grinders are approved for use with burrs up to a Ø of 12 mm.

Manufacturer's designation: GSZ4-90EL

Power consumption: 350 W

Speed range: 3500 - 8500 rpm

maximum collet Ø: 6 mm

Weight: 1.5 kg

maximum vibration to EN: < 2.5 m/s²

Technical description

maximum vibration to EN	< 2.5 m/s ²
Weight	1.5 kg
Power consumption	350 W
Manufacturer's designation	GSZ4-90EL
electronic speed pre-selection	yes
Speed range	3500 - 8500 rpm
maximum collet Ø	6 mm

Accessories

Collet for straight grinder Collet Ø 6 mm	077268 6
---	----------