



Straight die grinder, Type: 722325



Order data

Order number	077261 722325
GTIN	4014586880648
Item class	03F

Description

Version:

- **Exceptionally handy straight die grinder.**
- **Quiet running due to multiple spindle bearings.**
- **Powerful motor with high cutting power.**
- **Due to speed regulation, outstandingly suitable for cutting stainless steel, and also for grinding and polishing work.**
- **Suitable for grinding points and carbide milling cutters.**

Universal straight die grinder for working where access is difficult. Handy, slim neck enables internal grinding.

- **Exceptionally handy straight die grinder.**
- **Suitable for grinding stainless steel and for light grinding and polishing work.**
- **Narrow grinding head for inaccessible places.**
- **Variable speed enables the use of different tools.**

Supplied with:

Collet \varnothing 6 mm, 2 chuck wrenches 13 AF and 17 AF.

Note:

Straight die grinders are approved for use with burrs up to a \varnothing of 12 mm.

Technical description

Cable length	4 m
maximum vibration to EN	$< 2.5 \text{ m/s}^2$

Weight	1.5 kg
Power consumption	350 W
Manufacturer's designation	GSZ4-90EL
electronic speed pre-selection	yes
Speed range	3500 - 8500 min ⁻¹
maximum collet Ø	6 mm
Power supply	Mains operated
Type of product	Straight die grinder

Accessories

Collet for straight grinder Collet Ø 6 mm	077268 6
---	----------