

Garant**Bit ratchet plug-in head, Bit-holder: 1/4in****Order data**

Order number	657932 1/4
GTIN	4062406229641
Item class	61E

Description**Version:**

Drop-forged; all plug-in heads = Rectangular shank with spring retaining pin. This ensures a solid and secure fit of the plug-in head in the torque wrench.

Ratchet reversible for clockwise / anticlockwise tightening.

Application:

To take bits with hexagon shank to DIN ISO 1173 C 6.3 and E 6.3 (1/4 inch).

Material:

Chrome vanadium steel, chrome-plated.

Cutting dataa:**Legend for drawing and formula:**

l_1 = Lever length without plug-in head

l_2 = Adjusted reference dimension on the torque wrench

l_3 = Lever length including factory calibration reference dimension

l_4 = Reference dimension of the plug-in head

L = Total length of the tool

T_1 = Torque to be set

T_2 = Specified torque

Suitable for:

Torque wrench with rectangular sockets.

Note:

The rated load on this plug-in head is limited to the corresponding jaw width, and may be less than that of the torque wrench.

Please note the pitch of the plug-in head and match this to that of the adjustment tool (see test certificate/operating instructions of the torque wrench you are using). If these vary, correct the pitch!

Technical description

Width b	17.5 mm
Exchangeable tool	Plug-in head
Long-term rated loading	15 Nm
No. of teeth	60
Bit-holder	1/4 in
Plug-in shank	9×12 mm
Pitch S	17.5 mm
Height h	12.4 mm
Material	Chrome vanadium steel
Ratchet reversible	yes
Tool with ratchet function	yes
Type of product	BIT ratchet socket plug-in head