



ER collet chuck Form AD, BT 40 A = 100, for ER collet size: 40



Order data

Order number	302767 40
GTIN	4062406230074
Item class	32A

Description

Version:

External and internal taper ground.

- **All shanks fine bead blasted. Balancing quality G6.3 / 18,000 rpm.**
- **High-quality precision clamping nut.**

Application:

For clamping tools with parallel shank in collets to **DIN 6499 Form A and B.**

Supplied with:

ER clamping nut.

Optional extras:

ER collets No. 308881 – 309434, ER chuck keys No. 309680 – 309745 or No. 613300.

Pull studs (PS) No. 308760 – 308806. Pull stud wrenches No. 308820; 308835.

Note:

Matching clamping nut No. 309580 or 309610.

Machining strategy: HPC

Clamping range: 3 - 26 mm

Overhang dimension A: 100 mm

External Ø D: 63 mm

Spare ER clamping nut: 40

ER chuck key: 40

Technical description

ER chuck key	40
--------------	----

Clamping range	3 - 26 mm
Spare ER clamping nut	40
Overhang dimension A	100 mm
External Ø D	63 mm
Adapter	BT 40 A = 100
Arbor standard	JIS B6339
Arbor standard	JIS B6339
Shape	AD
Concentricity	≤ 3 µm
Machining strategy	HPC
Type of product	Collet chuck

Accessories

ER chuck key for ER collet chuck 40	309680 40
-------------------------------------	-----------