

**Bore plug gauge for through holes OD stainless, Sleeve Ø D: 80-100mm****Order data**

Order number	435157 80-100
GTIN	2050001951212
Item class	46D

**Description****Version:**

OD bore plug gauges are mechanical two-point dial bore plug gauges for highest requirements. Hardened gauging sleeve. For bores of 3 – 100 mm. Centring by the gauging sleeve prevents tilt errors and therefore ensures maximum precision irrespective of the user. No need to seek the return point. Dial indicators with shank Ø 8 h6 can be used as displays.

- **Repetition accuracy 1 µm.**
- **Robust and reliable.**
- **Minimum measuring time with maximum measuring reliability.**
- **Thread connection bore gauge/ holder M10×1.**

Measuring sleeve made of stainless steel against corrosion.

**Application:**

For bores of 3 – 100 mm. For quality assurance in series production, manual or automatic measuring.

**Supplied with:**

Gauging sleeve with two radially movable 180° offset carbide measuring bars.

**Optional extras:**

Precision dial comparator No. 434674, inductive precision dial comparator No. 434670, dial indicator with anticlockwise scale 434807 size 10, digital dial indicator 434322, holder for plug gauges No. 435160, setting rings No. 484030. Measuring depth extensions, angle pieces and depth stops on request.

**Note:**

When ordering, please state **additionally** the exact bore tolerances, for example:

No. 435154 size 6–12 **10H7**,

No. 435154 size 6–12 **10 + 0.15 / – 0.01**,

No. 435154 size 6–12 **9.990 / 10.15.**

When using precision dial indicators, an additional extension No. 434920 size 10 or probe No. 434900 size 16 is required.

- **Plug gauges for large bores (up to Ø 500), recesses, grooves, also in 3-point version available on request.**
- **Tolerance range 10 µm or fine fit quality 5 and finer on request.**
- **Measuring range > 0.2 mm on request.**
- **Measuring contacts with larger radius as well as in ruby, ceramic and DLC-coated are available.**

## Technical description

Sleeve dimension H	33 mm
Face dimension h	10 mm
Gauging force	2 N
Repetition accuracy	1 µm
Tolerance zone	V
Tolerance zone	U
Tolerance zone	T
Tolerance zone	B
Tolerance zone	R
Tolerance zone	S
Tolerance zone	P
Tolerance zone	N
Tolerance zone	M
Tolerance zone	K
Tolerance zone	J
Tolerance zone	JS
Tolerance zone	G
Tolerance zone	H
Tolerance zone	A
Tolerance zone	FG
Tolerance zone	EF

Tolerance zone	F
Tolerance zone	E
Tolerance zone	D
Tolerance zone	CD
Tolerance zone	C
Tolerance zone	ZB
Tolerance zone	ZC
Tolerance zone	ZA
Tolerance zone	Z
Tolerance zone	FG
Tolerance zone	ZC
Quality	10 mm
Quality	6 mm
Quality	7 mm
Quality	11 mm
Quality	13 mm
Quality	9 mm
Quality	12 mm
Quality	8 mm
Nominal size	80 - 100 mm
Material	Stainless steel, INOX
Calibration	C4
Type of product	Bore gauge micrometer head

## Services

Calibration Precision bore gauge (types B + C) maximum measuring range 160 mm

023210 160

## Accessories

Holder for plug gaugeOD Holder length 105 mm

435160 105