



## Cordless sheet metal slitters / shears, Type: 7130036



### Order data

Order number	078100 7130036
GTIN	
Item class	03F

### Description

#### Version:

Cordless sheet metal slitter for mobile use.

#### Sheet metal slitter.

- **Distortion-free cut.**
- **Open cutting head for best view on to the cut.**
- **QuickIN quick-change system for quick blade changing without tools or adjustment.**

#### Supplied with:

Cordless lamp **without** battery and **without** charger.

#### Note:

See No. 073832 and No. 073845 for suitable batteries and chargers.

### Technical description

suitable battery - supplier / battery type / voltage	Fein type E 18 V
Radius of the smallest curve	90 mm
Packaging	Carrying case
maximum vibration to EN	< 2.5 m/s <sup>2</sup>
Rate of strokes	3500 min <sup>-1</sup>
Manufacturer's designation	ABSS 18 1.6E

maximum material thickness steel 400&nbsp;N/mm <sup>2</sup>	1.6 mm
Battery voltage	18 V
Cutting speed	5 - 8 m/min
maximum material thickness steel 800&nbsp;N/mm <sup>2</sup>	0.8 mm
Cutting width	5 mm
Weight	1.9 kg
Number of rechargeable batteries contained	0
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Type of product	Aviation snips

---

## Accessories

Li-ion battery Rechargeable battery type, battery voltage FE18 V	073835 FE18
Li-ion battery Rechargeable battery type, battery voltage FE18 V	073837 FE18