

KÄRCHER**Industrial vacuum cleaner, Manufacturer's designation: IVR-L100DP****Order data**

Order number	078522 IVR-L100DP
GTIN	4054278275864
Item class	07D

Description**Version:**

Industrial vacuum cleaner suitable for vacuuming up and separating **coolants, lubricating emulsions, water or oil with solids (e.g. metal chips)**.

- **Compact design and robust materials for the best movement characteristics.**
- **Maximum flexibility in use and long working life for the oil-resistant power cable.**
- **Suction is applied via a 360° rotatable hose connection on the suction head.**

2-motor 2.4 kW industrial vacuum cleaner with **tilting mobility trolley, 100 litre stainless steel tank and integral barrel pump** for easy and complete emptying.

Supplied with:

With tilting chassis, and drain hose with level indicator. **Without accessories. Suitable accessories can be found under No. 078524, 078529 and 078533.**

Note:

A version with 100-litre stainless steel container can be found under No. 078522 size IVR-L100DP in our eShop.

Technical description

Operating noise	76 dB(A)
-----------------	----------

Cable length	6 m
Manufacturer's designation	IVR-L 100/24-2 Tc M
Width	620 mm
Connection width	DN50 mm
Number of turbines	2
Length	740 mm
Power consumption	2400 W
Air flow volume	118 l/s
Weight	59 kg
Container volume	100 l
Vacuum	230 mbar
Dust class – vacuum cleaner	L
Height	1180 mm
Power supply	Mains operated
Type of product	Wet and dry vacuum cleaners

Accessories

Set for vacuuming chips and liquids Connection width DN50	078529 DN50
Fine fleece for swarf basket 40l. suitable for vacuum cleaner type IVR-L100	072806 IVR-L100
Swarf basket for the industrial vacuum cleaner Volume 40 l	078524 40