



Temperature scanner HL Scan, Type: 014919



Order data

Order number	078326 014919
GTIN	4007841014919
Item class	07E

Description

Version:

Temperature scanner for sensing the temperature at the surface of the workpiece by means of infra-red measurement. Ideal determination of distance by laser. Acoustic and visual warning if the optimum temperature is overshoot or undershot. Setting in 10 °C steps.

HL Scan with LCD display and 9 V battery.

Description:

The HL Scan temperature scanner monitors the workpiece temperature using an LED beam. An acoustic and visual warning signal is output if the permissible temperature is overshoot or undershot.

Suitable for :

For the HL 1920 E and HL 2020 E, and the HG 2120 E and HG 2320 E professional devices.

Weight: 165 g

Temperature recording range: 0 - 300 °C

suitable for: HG 2320, HG 2120

Technical description

Weight	165 g
Temperature recording range	0 - 300 °C
suitable for	HG 2320, HG 2120
Battery type	9 V block
Number of batteries contained	1
Power supply	Battery-powered

Type of product

Temperature scanner