

**KÄRCHER**
**Industrial vacuum cleaner, Manufacturer's designation: IVR-L100TC**

**Order data**

Order number	078522 IVR-L100TC
GTIN	4054278275840
Item class	07D

**Description**
**Version:**

Industrial vacuum cleaner suitable for vacuuming up and separating **coolants, lubricating emulsions, water or oil with solids (e.g. metal chips)**.

- **Compact design and robust materials for the best movement characteristics.**
- **Maximum flexibility in use and long working life for the oil-resistant power cable.**
- **Suction is applied via a 360° rotatable hose connection on the suction head.**

2-motor 2.4 kW industrial vacuum cleaner with **tilting mobility trolley** and **100 litre tank**.

**Supplied with:**

With tilting chassis, and drain hose with level indicator. **Without accessories. Suitable accessories can be found under No. 078524, 078529 and 078533.**

**Note:**

A version with 100-litre stainless steel container can be found under No. 078522 size IVR-L100DP in our eShop.

**Technical description**

Dust class – vacuum cleaner	L
Dust class – vacuum cleaner	L

Connection width	DN50 mm
Power consumption	2400 W
Width	660 mm
Weight	58 kg
Air flow volume	148 l/s
Vacuum	230 mbar
Manufacturer's designation	IVR-L 100/24-2 Tc
Container volume	100 l
Operating noise	68 dB(A)
Height	1320 mm
Length	840 mm
Cable length	6 m
Number of turbines	2
Power supply	Mains operated
Type of product	Wet and dry vacuum cleaners

## Accessories

Set for vacuuming chips and liquids Connection width DN50	078529 DN50
Swarf basket for the industrial vacuum cleaner Volume 40 l	078524 40