

Mitutoyo**Vernier caliper, Measuring range: 300mm****Order data**

Order number	412101 300
GTIN	4946368110196
Item class	44A

Description**Version:**

Satin chromium plated anti-glare scales.

Fine, high-contrast scale.

Locking screw at the top.

Precision ground measuring faces.

Optional extras:

Thread table No. 412180 for caliper back.

Technical description

Length of cross tips	22 mm
Measuring range	300 mm
Packaging	Wallet
Reversible reading	mm / inch
Graduation	1/20 mm
Graduation	1/128 in
Calibration	A1
Scale divisions	0.05 mm
Jaw length	64 mm
Standard	ISO 13385
Weight	355 g

Depth gauge	rectangular 3.7×1.4
Depth gauge available	yes
Measurement deviation E MPE	± 0.08 mm
Scale chrome plated	yes
Locking	Locking screw at top
Guidance	Raised slides
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Type of product	Universal calipers

Services

DAkkS calibrationCalipers / depth gauges maximum measuring range 300 mm	021010 300
CalibrationCalipers / depth gauges maximum measuring range 300 mm	021000 300

Accessories

Depth gauge holder, metal with 2 screws	412120
Plastic case Type MS300	412470 MS300