

**Angle grinder GWS, Type: 26-230LVI****Order data**

Order number	077153 26-230LVI
GTIN	3165140660570
Item class	03C

Description**Version:****Powerful 230 mm angle grinder:**

- **Powerful motor with constant-speed electronics, smooth start-up and inrush current limitation.**
- **High protection of the user by vibration control on the main and auxiliary handles, kick-back stop and restart inhibit.**
- **Adjustable grasp handle for optimum grinding and cutting.**
- **SDS quick-clamping nut and spindle lock.**

2600 W Motor, **PROtection switch**, which switches the machine off immediately the trigger is released.

Supplied with:

Supplied with protective hood, additional handle.

With SDS quick-clamping nut.

Manufacturer's designation: GWS 26-230 LVI

Power consumption: 2600 W

maximum speed: 6,500 min⁻¹

maximum disc Ø: 230 mm

maximum cutting depth: 69 mm

Weight: 5.6 kg

Technical description

Restart block	yes
Power consumption	2600 W

maximum speed	6,500 min ⁻¹
Kick-back stop	yes
maximum cutting depth	69 mm
Weight	5.6 kg
maximum vibration to EN	6 m/s ²
maximum disc Ø	230 mm
Soft start	yes
Special features	Constant-speed electronics, PROtection switch
Manufacturer's designation	GWS 26-230 LVI
Power supply	Mains operated
Type of product	Angle grinder