

Garant
Solid carbide HPC drill plain shank DIN 6535 HA, TiAlN, Ø DC h7: 10,2mm

Order data

Order number	122760 10,2
GTIN	4045197057891
Item class	11E

Description
Version:

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**.

Convex cutting edges with honed edges and special flute profile for **short chips**, even on long chipping materials.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Form HB and HE supplied at the same price as HA.

Form **HB**: order with **No. 122765**.

Form **HE**: order with **No. 122760 + 129100HE**.

NEW GENERATION AVAILABLE!

Recommended successor products are No. 122715; 122725 and 122651.

Technical description

Number of cutting edges Z	2
Nominal Ø D _c	10.2 mm
Shank tolerance	h6
Flute length L _c	71 mm
Feed f in steel < 1100 N/mm ²	0.27 mm/rev.
Tolerance nominal Ø	h7
Shank Ø D _s	12 mm
Overall length L	118 mm

Standard	DIN 6537
recommended maximum drilling depth L ₂	55.7 mm
Coating	TiAlN
Tool material	Solid carbide
Version	6×D
Point angle	140 degrees
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	green
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Steel < 500 N/mm ²	suitable only under restricted conditions	120 m/min	P
Steel < 750 N/mm ²	suitable	100 m/min	P
Steel < 900 N/mm ²	suitable	85 m/min	P
Steel < 1100 N/mm ²	suitable	65 m/min	P
Steel < 1400 N/mm ²	suitable	35 m/min	P
Steel < 55 HRC	suitable	28 m/min	H
INOX < 900 N/mm ²	suitable only under restricted conditions	30 m/min	M
Ti > 850 N/mm ²	suitable only under restricted conditions	35 m/min	S
GG(G)	suitable	70 m/min	K
Uni	suitable		
wet maximum	suitable		
Air	suitable		

Services

Shank grinding Type HE

129100 HE