

**FLEX**
**TRINOX FLEX burnishing machine, Type: SET**

**Order data**

Order number	077751 SET
GTIN	4030293187184
Item class	03S

**Description**
**Version:**

**Powerful TRINOFLEX BSE 14-3 100 burnishing machine with constant-speed electronics.**

- **Speed pre-selection and stability by means of a tacho generator.**
- **Soft start, overload protection and restart inhibit after a power failure.**
- **Electronics module completely encapsulated, thereby preventing damage by ingress of dust.**

Unique tool attachment with quick-release coupling for changing the modular attachments "Burnishing" and "Pipe finishing" without tools.

**Application:**

For burnishing, polishing, brushing, smoothing, rust removal and deburring.

**Supplied with:**

Burnishing machine BSE14-3 100, 1 burnishing attachment BS100. Supplied with 1 pc. burnishing attachment BS 100, 1 pc. rubber air roller, 1 pc. air pump, 1 pc. abrasive fleece A 280/fine, 17-piece abrasive sleeve set, 1 pc. carrying case L-BOXX® 238.

15-piece abrasive sleeve set consisting of:

- **1 pc. abrasive sleeve MESHFLEX A 400.**
- **3 pcs. each of abrasive sleeves ZIRCOFLEX P 80; P 120.**
- **3 pcs. abrasive sleeves CERAFLEX K 120.**
- **3 pcs. abrasive sleeves CORUFLEX P180.**
- **1 pc. each of superfinishing sleeve S600; S 1500.**

**Technical description**

Toolholder	19
Speed range	1000 - 3500 min <sup>-1</sup>
maximum vibration to EN	0 m/s <sup>2</sup>
Polishing tool length	100 mm
Weight	2.9 kg
Power consumption	1400 W
Packaging	Carrying case
maximum polishing tool Ø	125 mm
Manufacturer's designation	BSE 14-3 100 set
Power supply	Mains operated
Type of product	Burnishing machine