



Deburring and chamfering machine, Type: EKF300



Order data

Order number	078121 EKF300
GTIN	4250187507229
Item class	07E

Description

Version:

Chamfering machine with smooth start-up and thermal overload protection for machining straight edges, internal and external radii and holes from 22 mm Ø. Fine adjustment permits light chamfering for deburring and also wide chamfering. With improved cutter head for reduced cutting forces. Chamfer 30° – width stepless 0 - 5 mm.

Supplied with:

Milling head, **3 carbide** inserts, swarf hook No. 084520 and transport case.

Note:

A component edge height of at least 2 mm is necessary to provide guidance.

Technical description

Length	310 mm
AC supply voltage	230 V
Power consumption	1500 W
Weight	4 kg

maximum speed	6000 min ⁻¹
Height	295 mm
Manufacturer's designation	EKF300
Width	138 mm
Chamfer	30°
Power supply	Mains operated
Packaging	Carrying case
Type of product	Deburring and chamfering machine

Accessories

Carbide insert set, 3 pieces, SHM 200for steel Type SHM200	078128 SHM200
Milling tool3-cutter Type ZFR300	078133 ZFR300
Spare screw for EKF inserts Version SCREW	078127 SCREW