

**Battery / mains radio, Type: M18JSRDAB****Order data**

Order number	073960 M18JSRDAB
GTIN	4002395167760
Item class	03L

**Description****Version:**

Sturdy site radio, splash-proof (IP54) for mains and battery operation.

- **USB port for charging mobile devices.**
- **AUX input for connecting external audio playback devices.**
- **LCD digital clock with batteries.**
- **Operation with Milwaukee 18 volt batteries or with 220-240 volt AC voltage.**

High-performance audio system with DAB+ digital radio and FM tuner.

- **Two speakers with passive membranes generate a loud and clear sound with rich bass.**
- **Digital tuner with 10 memory spaces.**
- **Robust design protects the radio against splashed water and dust on building sites.**
- **Compartment for secure storage of MP3 player.**

**Function:**

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

**Supplied with:**

Includes mains cable, 2 back-up batteries, AUX connection cable, without batteries.

**Technical description**

Width	200 mm
-------	--------

Weight	5 kg
Manufacturer's designation	M18JSRDAB+-0
Length	400 mm
Interface	USB interface
Battery voltage	18 V
Height	200 mm
Number of rechargeable batteries contained	0
IP Index of Protection	IP 54
Power supply	Rechargeable battery-powered
Power supply	Mains operated
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Type of product	Radio

## Accessories

Battery charger Type M1218FC	073840 M1218FC
Li-ion system M18B5 Battery type MB18	073816 MB18
Battery charger Type M1218C	073840 M1218C