

## Garant

### Solid carbide drill plain shank for uni-directional fibre orientation DIN 6535 HA, Diamond, Ø DC m7: 11mm



#### Order data

Order number	122522 11
GTIN	4045197465924
Item class	11Y

#### Description

##### Version:

With the latest generation of **crystalline diamond coating sp<sup>3</sup>**, for process reliability in machining **fibre-reinforced composites, CRP, GRP, and graphite. With 90° point angle** and special geometry to **avoid delamination.**

**With cutting guide chamfer** to avoid delamination, projecting fibres, and burr formation on materials with **uni-directional** fibre orientation.

##### Note:

Flute length  $L_c = L_2 + 1.5 \times D_c$

Available in **1/100 sizes** and according to the table.

**Please note the minimum order quantities for configurable sizes:**

Ø range 1.01 – 2.99 mm: **10 pieces**

Ø range 3.01 – 9.99 mm: **5 pieces**

Ø range 10.01 – 11.99 mm: **3 pieces**

#### Technical description

Flute length $L_c$	71 mm
Nominal Ø $D_c$	11 mm
Shank tolerance	h6
Feed $f$ in GRP CRP	0.19 mm/rev.
Number of cutting edges $Z$	2
Tolerance nominal Ø	m7
Shank Ø $D_s$	12 mm

Overall length L	118 mm
recommended maximum drilling depth L <sub>2</sub>	54.5 mm
Coating	Diamond
Tool material	Solid carbide
Standard	Manufacturer's standard
Version	5×D
Point angle	90 degrees
Shank	DIN 6535 HA to h6
Through-coolant	no
Colour ring	black
Type of product	Jobber drill

## User data

	Suitability	V <sub>c</sub>	ISO code
PMMA acrylic	suitable only under restricted conditions	150 m/min	N
PE-HD	suitable only under restricted conditions	140 m/min	N
PA 66	suitable only under restricted conditions	130 m/min	N
PEEK	suitable only under restricted conditions	120 m/min	N
PF 31	suitable only under restricted conditions	100 m/min	N
PVDF GF20	suitable	110 m/min	N
POM GF25	suitable	100 m/min	N
PA 66 GF30	suitable	90 m/min	N
PEEK GF30	suitable	80 m/min	N
PTFE CF25	suitable	90 m/min	N
PEEK CF30	suitable	80 m/min	N

Hybrids	suitable		
GRP, CRP	suitable	100 m/min	N
Graphite	suitable	340 m/min	N
wet maximum	suitable only under restricted conditions		
dry	suitable		
Air	suitable		