

# Solid carbide drill IC plain shank unidirectional DIN 6535 HA, Diamond, Ø DC m7: 6 mm



### Order data

Order number	122532 6
GTIN	4045197506900
Item class	11Y

# Description

#### **Version:**

With the latest generation of **crystalline diamond coating sp**<sup>3</sup>, for process reliability in machining **fibre-reinforced composites**, **CRP**, **GRP**, **and graphite**. **With 90° point angle** and special geometry to**avoid delamination**.

Under optimum conditions of use, the **double flute face** can generate high precision holes (roundness < 15  $\mu$ m to base tolerance IT 7). Low heat generation due to internal cooling permits higher speeds and feeds.

## **Recommendation:**

### **Maximum drilling depth:**

Flute length (see table) less  $1.5 \times nominal \emptyset$ .

#### Note:

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

Available in **1/100 sizes** and according to the table.

Tolerance nominal Ø: m7 Number of cutting edges Z: 2

recommended maximum drilling depth L<sub>2</sub>: 35 mm

Overall length L: 82 mm Shank Ø D<sub>4</sub>: 6 mm

Feed f in GRP CRP: 0.11 mm/rev.

# **Technical description**

Flute length L <sub>c</sub>	44 mm
Number of cutting edges Z	2
Feed f in GRP CRP	0.11 mm/rev.

Nominal Ø D <sub>c</sub>	6 mm
Shank tolerance	h6
Tolerance nominal Ø	m7
Shank Ø D <sub>s</sub>	6 mm
Overall length L	82 mm
recommended maximum drilling depth L <sub>2</sub>	35 mm
Coating	Diamond
Tool material	Solid carbide
Standard	Manufacturer's standard
Drill depth up to	5×D
Point angle	90 degrees
Cutting direction	right-hand
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 25 bar
Colour ring	black
Type of product	Jobber drill