

HEDI

Machine / workstation lamp, Type: 6LEDDUO



Order data

Order number	081300 6LEDDUO
GTIN	4003644000135
Item class	08B

Description

Version:

High quality, universally usable lamps for 250 V / 50 Hz with On / Off switch, 3 m rubber connection cable.

Robust, long, coated flexible metal arm for good mobility of the lamp head and high stability.

Can be switched from flood to spot beam, lamp head can be **turned and swivelled 340°** using the ball joint.

Machine lamp with **LEDs** for directed illumination of the work place. Low power consumption, avoids heating up the illuminated objects and subjecting them to UV radiation.

Standard:

High quality, universally usable lamps for 250 V / 50 Hz with On / Off switch, 3 m rubber connection cable.

- **Sturdy, long, coated flexible metal arm.**

Supplied with:

Bulb, with **strong magnetic clamp, 50 mm screw-on clamp, and mounting screws** for machine, table, wall or ceiling attachment.

Attention:

German version. Order free UK adapter plug No. 08 1172_GB.

Note:

Available in warm white (3,000 K).

IP Index of Protection: IP 20

Light output: 6 W
Illumination: 450 lm
Number of LEDs: 4
Connection cable length: 3 m
Energy efficiency class : A

Technical description

Number of LEDs	4
Connection cable length	3 m
Illumination	450 lm
Power supply	Mains-powered
Bulb	LED
Energy efficiency class	A
IP Index of Protection	IP 20
Light colour	6,400 K
Lamp replaceable	yes
Light output	6 W

Accessories

Spare bulb suitable for type 6LED	081310 6LED
-----------------------------------	-------------