



## Cordless chainsaw, Type: M18FCHS121



### Order data

Order number	078203 M18FCHS121
GTIN	4058546221683
Item class	03L

### Description

#### Version:

- **Sturdy chainsaw with excellent ergonomics, high performance and high chain speed.**
- **18-V Li-ion battery offers you similar performance, reliable operation and service life to a petrol-driven garden device – but without direct emissions.**
- **With one battery charge, you can handle up to 150 cuts in 10×10 cm softwood (12.0 Ah); the same amount of work as one fill of the tank for a petrol garden device.**
- **The REDLITHIUM™-ION HIGH OUTPUT™ 12.0-Ah battery has been developed for professional and long-lasting use and fits all hand-held Milwaukee cordless power tools. You can therefore use the same battery for your Milwaukee cordless sabre saws, cordless angle grinders or cordless hammer drills / drivers.**
- **Metallic claw stop for improved leverage during the cutting process.**
- **Simple chain lubrication: leak-free container for chain oil (tank contents 200 ml), easy to fill, simple level monitoring.**

#### Supplied with:

Including 12.0-Ah High-Output battery and charger, 80 ml of oil, chain and chain protection (sheath).

### Technical description

Weight	6.4 kg
Battery capacity	12 Ah
Number of rechargeable batteries contained	1
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V

maximum vibration to EN	4.96 m/s <sup>2</sup>
Battery voltage	18 V
Noise pressure level	97.69 dB
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Type of product	Chainsaw