

## Garant

**Pair of wheeled subframes for a mobile drawer cabinet Direction of pushing from the front of the drawer, Type: R27E**



### Order data

Order number	942947 R27E
GTIN	4045197806444
Item class	91H

### Description

#### Version:

Pair of wheeled subframes - 2 ball-bearing mounted wheels and 2 castors (Ø 100 mm) with parking brake, each linked by a transverse subframe. **Note the movement direction of the wheels.** Load capacity 600 kg evenly distributed.

#### Suitable for:

Pair of wheeled subframes to fit tool cabinet shells of product group 94 (up to 08/2019) with **dimensions 27×27 units**. For reasons of safety (risk of tipping over) the maximum usable height of the body is limited to 800 mm. **Push the cabinet from the front of the drawers.**

#### Note:

- **Drawers in mobile tool cabinets must be fitted with individual drawer locking. This locks the drawer automatically on closing, so that it cannot open during transport. Individual drawer locking for drawers in product group 94 (up to 08/2019) can be found under No. 949605 in the spare parts list.**
- **When checking that the load capacity of the wheels (600 kg) is not exceeded, please make allowance for the tare weight of the cabinet itself.**
- **Please note the desired direction of movement of the wheels.**

### Technical description

Fixed wheel Ø	100 mm
---------------	--------

total maximum load capacity	600 kg
Castor Ø	100 mm
Type of product	Roller