



## Pneumatic screwdriver, Type: S2480

### Order data

Order number	079161 S2480
GTIN	4589484319243
Item class	03R

### Description

#### Version:

All technical data relate to a dynamic pressure of **6.3 bar** and the specified hose internal Ø. Versatile application screwdrivers with 1/4 inch hexagon socket quick-release chuck for E 6.3 bits (see No. 674200 ff), reversible for **clockwise / anticlockwise** rotation. With impact mechanism (low reset torque).

#### Spare part:

**Selected service kits:** Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

Torque range: 6 – 13 N·m

maximum screw Ø (8.8 - 12.9): M5

maximum speed: 6500 min<sup>-1</sup>

Tool arbor size: 1/4 in

maximum air consumption: 600 l/min

Connection thread: BSP

### Technical description

Weight	0.78 kg
maximum vibration to EN	6.4 m/s <sup>2</sup>
Tool arbor size	1/4 in
recommended hose size (internal Ø)	10 mm
maximum speed	6500 min <sup>-1</sup>
Manufacturer's designation	S2480
maximum air consumption	600 l/min
Torque range	6 – 13 N·m

## Data sheet

Operating noise	90 dB(A)
maximum screw Ø (8.8 - 12.9)	M5
Length	132 mm
Compressed air connection	1/4 in
Connection thread	BSP