



Pneumatic impact wrench 3/8 inch – 1/2 inch, Type: 7739



Order data

Order number	079202 7739
GTIN	015451591304
Item class	03R

Description

Version:

Robust impact wrench with **convenient one-hand changeover using Side-2-Side technology**, composite casing with thermal insulation properties and robust double hammer impact drive. Balanced weight distribution for more comfortable working. Exhaust air is directed downwards through the handle. **Tightening power can be regulated in steps.**

Torque range: 68 - 414 N·m

Maximum screw Ø (8.8 - 12.9): M20

maximum speed: 9900 min⁻¹

Tool arbor drive profile: Square

Tool arbor size: 1/2 in

maximum air consumption: 564 l/min

Technical description

maximum speed	9900 min ⁻¹
Weight	1.2 kg
Tool arbor drive profile	Square

recommended hose size (internal Ø)	10 mm
Length	163 mm
Tool arbor size	1/2 in
Operating noise	92 dB(A)
maximum vibration to EN	6.4 m/s ²
maximum air consumption	564 l/min
Torque range	68 - 414 N·m
Maximum screw Ø (8.8 - 12.9)	M20
Manufacturer's designation	7739
Compressed air connection	1/4 in
Connection thread	NPT
Type of product	Screwdriver