

Garant
GARANT Master Mute boring bar shank vibration damping, 8×D, System / shank Ø: GL/16

Order data

Order number	264866 GL/16
GTIN	4062406231408
Item class	29E

Description
Supplied with:

Reducing adaptor for coolant connection.

Note:

Do not clamp on the area marked S!

$D_{\min} = 1/2 \text{ shank } \varnothing + \text{cutting head centre-line offset } L_3.$

Convenient boring bar orientation by set-up head No. 265001.

Technical description

non-clamping range S	74 mm
recommended clamping length	64 mm
System	GL
Assembly bolt set	269026 1
Overall length L	170 mm
suitable interchangeable cutting heads	264830; 264831
Series	Master Mute
Boring depth up to	8×D
Vibration	damped
Through-coolant	yes
Type of product	Boring bar shanks

