

Garant
GARANT Master Mute boring bar shank vibration damping, 8×D, System / shank Ø: QC/20

Order data

Order number	264890 QC/20
GTIN	4062406231170
Item class	29E

Description
Supplied with:

Reducing adaptor for coolant connection.

Note:

Do not clamp on the area marked S!

$D_{\min} = 1/2 \text{ shank } \varnothing + H + \text{cutting head centre-line offset } L_3.$

Convenient boring bar orientation by set-up head No. 265001.

Through-coolant: yes

System: QC

Overall length L: 200 mm

non-clamping range S: 84 mm

recommended clamping length: 80 mm

Assembly bolt set: 269026 1

Technical description

recommended clamping length	80 mm
System	QC
non-clamping range S	84 mm
Assembly bolt set	269026 1
Plug connector for coolant connection	269208
High-pressure connecting hose	269207
Overall length L	200 mm

suitable interchangeable cutting heads	264834; 264835
Series	Master Mute
Boring depth up to	8×D
Vibration	damped
Through-coolant	yes
Type of product	Boring bar shanks