

**Garant**
**GARANT Master Mute boring bar shank vibration damping, 8×D, System / shank Ø: QC/32**

**Order data**

Order number	264890 QC/32
GTIN	4062406231194
Item class	29E

**Description**
**Supplied with:**

Reducing adaptor for coolant connection.

**Note:**

Do not clamp on the area marked S!

$D_{\min} = 1/2 \text{ shank } \varnothing + H + \text{cutting head centre-line offset } L_3.$

Convenient boring bar orientation by set-up head No. 265001.

Through-coolant: yes

System: QC

Overall length L: 320 mm

Centre offset H base body: 6 mm

non-clamping range S: 124 mm

recommended clamping length: 128 mm

Assembly bolt set: 269026 1

**Technical description**

Centre offset H base body	6 mm
non-clamping range S	124 mm
System	QC
recommended clamping length	128 mm
Assembly bolt set	269026 1
Plug connector for coolant connection	269208
High-pressure connecting hose	269207

Overall length L	320 mm
suitable interchangeable cutting heads	264834; 264835
Series	Master Mute
Boring depth up to	8×D
Vibration	damped
Through-coolant	yes
Type of product	Boring bar shanks