

Garant
GARANT Master Mute boring bar shank vibration damping, 11×D, System / shank Ø: QC/32

Order data

Order number	264894 QC/32
GTIN	4062406231323
Item class	29E

Description
Supplied with:

Reducing adaptor for coolant connection.

Note:

Do not clamp on the area marked S!

$D_{min} = 1/2 \text{ shank } \varnothing + H + \text{cutting head centre-line offset } L_3.$

Convenient boring bar orientation by set-up head No. 265001.

Through-coolant: yes

System: QC

Overall length L: 416 mm

Centre offset H base body: 6 mm

non-clamping range S: 151 mm

recommended clamping length: 128 mm

Assembly bolt set: 269026 1

Technical description

Centre offset H base body	6 mm
non-clamping range S	151 mm
System	QC
recommended clamping length	128 mm
Assembly bolt set	269026 1
High-pressure connecting hose	269207
Plug connector for coolant connection	269208

Overall length L	416 mm
suitable interchangeable cutting heads	264834; 264835
Series	Master Mute
Boring depth up to	11×D
Vibration	damped
Through-coolant	yes
Type of product	Boring bar shanks