

**Garant**
**GARANT Master Mute boring bar shank vibration damping, 8×D, System / shank Ø: DM/50**

**Order data**

Order number	264930 DM/50
GTIN	4062406231347
Item class	29E

**Description**
**Supplied with:**

Reducing adaptor for coolant connection.

**Note:**

Do not clamp on the area marked S!

$D_{\min} = 1/2 \text{ shank } \varnothing + H + \text{cutting head centre-line offset } L_3.$

Convenient boring bar orientation by set-up head No. 265001.

Through-coolant: yes

System: DM

Overall length L: 518 mm

Centre offset H base body: 5 mm

non-clamping range S: 179 mm

recommended clamping length: 200 mm

Assembly bolt set: 269026 3

**Technical description**

non-clamping range S	179 mm
Centre offset H base body	5 mm
recommended clamping length	200 mm
System	DM
Assembly bolt set	269026 3
Plug connector for coolant connection	269208
High-pressure connecting hose	269207

Overall length L	518 mm
suitable interchangeable cutting heads	264838; 264839
Series	Master Mute
Boring depth up to	8×D
Vibration	damped
Through-coolant	yes
Type of product	Boring bar shanks

---

## Accessories

Set of fastening screws Type 3	269026 3
--------------------------------	----------