

**Garant**
**GARANT Master Mute cutting head, right-hand, System / insert size: GL/11**

**Order data**

Order number	264830 GL/11
GTIN	4062406231446
Item class	29D

**Description**
**Suitable for:**

Boring bar shanks No. 264866, 264870 and 264874.

**Note:**

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: GL

Cutting point / joint: 16 mm

ISO code cutting head: SDUCR

suitable indexable insert: DC.. 0702..

Approach angle: 93 °

Minimum pre-drill  $\varnothing D_{\min}$ : 20 mm

Centre offset  $L_3$ : 11 mm

**Technical description**

Overall length L	16 mm
Minimum pre-drill $\varnothing D_{\min}$	20 mm

Insert screw	269028 38
System	GL
Centre offset L <sub>3</sub>	11 mm
Cutting point / joint	16 mm
Series	Master Mute
ISO code cutting head	SDUCR
Approach angle	93 °
suitable indexable insert	DC.. 0702..
Application type	right-hand
Through-coolant	yes
Type of product	Cutting head

---

## Accessories

Set of insert screws Type 38	269028 38
------------------------------	-----------