



Solid carbide high performance drill, Weldon shank DIN 6535 HB, TiAlN, Ø DC m7: 13,5mm



Order data

| | |
|--------------|---------------|
| Order number | 122406 13,5 |
| GTIN | 4045197424969 |
| Item class | 12E |

Description

Version:

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**. **Straight major cutting edges** with slightly honed edges and special flute profile produce **short chips**.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Technical description

| | |
|--|--------------|
| Feed f in stainless steel $< 900 \text{ N/mm}^2$ | 0.15 mm/rev. |
| Nominal $\varnothing D_c$ | 13.5 mm |
| Flute length L_c | 60 mm |
| Number of cutting edges Z | 2 |
| Shank tolerance | h6 |
| Tolerance nominal \varnothing | m7 |
| Shank $\varnothing D_s$ | 14 mm |
| Overall length L | 107 mm |
| Standard | DIN 6537 K |
| recommended maximum drilling depth L_2 | 39.8 mm |
| Coating | TiAlN |

| | |
|-----------------|-------------------|
| Tool material | Solid carbide |
| Version | 4xD |
| Point angle | 140 degrees |
| Shank | DIN 6535 HB to h6 |
| Through-coolant | yes, with 25 bar |
| Colour ring | blue |
| Type of product | Jobber drill |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Aluminium (short chipping) | suitable only under restricted conditions | 140 m/min | N |
| Alu > 10% Si | suitable only under restricted conditions | 120 m/min | N |
| Steel < 500 N/mm ² | suitable | 110 m/min | P |
| Steel < 750 N/mm ² | suitable | 90 m/min | P |
| Steel < 900 N/mm ² | suitable | 80 m/min | P |
| Steel < 1100 N/mm ² | suitable | 60 m/min | P |
| Steel < 1400 N/mm ² | suitable only under restricted conditions | 35 m/min | P |
| INOX < 900 N/mm ² | suitable | 45 m/min | M |
| INOX > 900 N/mm ² | suitable | 40 m/min | M |
| Ti > 850 N/mm ² | suitable | 30 m/min | S |
| GG | suitable only under restricted conditions | 70 m/min | K |
| wet maximum | suitable | | |
| wet minimum | suitable | | |
| Air | suitable | | |