

**Garant**
**Solid carbide HPC drill Weldon shank DIN 6535 HB, TiAlN, Ø DC h7: 15,8mm**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 122765 15,8   |
| GTIN         | 4045197399359 |
| Item class   | 11E           |

**Description**
**Version:**

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**.

**Convex cutting edges** with honed edges and special flute profile for **short chips**, even on long chipping materials.

**Note:**

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

**NEW GENERATION AVAILABLE!**

**Recommended successor products are No. 122716 and 122726.**

**Technical description**

|   |              |
|---|--------------|
| Feed f in steel < 1100 N/mm <sup>2</sup>          | 0.32 mm/rev. |
| Nominal Ø D <sub>c</sub>                          | 15.8 mm      |
| Shank tolerance                                   | h6           |
| Number of cutting edges Z                         | 2            |
| Flute length L <sub>c</sub>                       | 83 mm        |
| Tolerance nominal Ø                               | h7           |
| Shank Ø D <sub>s</sub>                            | 16 mm        |
| Overall length L                                  | 133 mm       |
| Standard  | DIN 6537     |
| recommended maximum drilling depth L <sub>2</sub> | 59.3 mm      |

|                    |                   |
|--------------------|-------------------|
| Coating            | TiAlN             |
| Tool material      | Solid carbide     |
| Version            | 6×D               |
| Point angle        | 140 degrees       |
| Shank              | DIN 6535 HB to h6 |
| Through-coolant    | yes, with 25 bar  |
| Machining strategy | HPC               |
| Semi-Standard      | yes               |
| Colour ring        | green             |
| Type of product    | Jobber drill      |

## User data

|                                | Suitability                               | V <sub>c</sub> | ISO code |
|--------------------------------|---|----------------|----------|
| Steel < 500 N/mm <sup>2</sup>  | suitable only under restricted conditions | 120 m/min      | P        |
| Steel < 750 N/mm <sup>2</sup>  | suitable                                  | 100 m/min      | P        |
| Steel < 900 N/mm <sup>2</sup>  | suitable                                  | 85 m/min       | P        |
| Steel < 1100 N/mm <sup>2</sup> | suitable                                  | 65 m/min       | P        |
| Steel < 1400 N/mm <sup>2</sup> | suitable                                  | 35 m/min       | P        |
| Steel < 55 HRC                 | suitable                                  | 28 m/min       | H        |
| INOX < 900 N/mm <sup>2</sup>   | suitable only under restricted conditions | 30 m/min       | M        |
| Ti > 850 N/mm <sup>2</sup>     | suitable only under restricted conditions | 35 m/min       | S        |
| GG(G)                          | suitable                                  | 70 m/min       | K        |
| Uni                            | suitable                                  |                |          |
| wet maximum                    | suitable                                  |                |          |
| Air                            | suitable                                  |                |          |

