



Die 6g, M: M24



Order data

Order number	140330 M24
GTIN	4062406233280
Item class	12K

Description

Version:

Closed, pre-slit form. **≥ M3 with tapered lead chamfer** on both sides for easy start to the threading action and clean swarf evacuation in the direction of cutting. **1 ¾ turns lead chamfer.**

Cutting direction: right-hand

Tolerance class: DIN 13 6g

Pitch: 3 mm

External Ø: 55 mm

Height: 22 mm

Technical description

External Ø	55 mm
Thread size	M24
Tolerance class	DIN 13 6g
Pitch	3 mm
Height	22 mm

Thread type	M
Flank angle	60 °
Tool material	HSS
Standard	EN 22568
Cutting direction	right-hand
Type of product	Die

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Oil	suitable		
dry	suitable only under restricted conditions		