



## Pneumatic screwdriver, Type: S2340

### Order data

Order number	079163 S2340
GTIN	7322590011413
Item class	03R

### Description

#### Version:

All technical data relate to a dynamic pressure of **6.3 bar** and the specified hose internal Ø.

- **With slip clutch.**
- **Adjustable torque setting.**
- **Reversible for clockwise/ anticlockwise rotation.**

Particularly suitable for series production screwdriving with quick-release bit holder for E 6.3 bits (see No. 674205 ff).

#### Spare part:

**Selected service kits:** Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

Torque range: 0.5 – 2 N·m

maximum screw Ø (8.8 - 12.9): M3

maximum speed: 1300 min<sup>-1</sup>

Tool arbor size: 1/4 in

Format: Rod

maximum air consumption: 240 l/min

### Technical description

Manufacturer's designation	S2340
maximum air consumption	240 l/min
Torque range	0.5 – 2 N·m
maximum vibration to EN	< 2.5 m/s <sup>2</sup>
Weight	0.9 kg
maximum screw Ø (8.8 - 12.9)	M3
Format	Rod

recommended hose size (internal Ø)	6.3 mm
Tool arbor size	1/4 in
maximum speed	1300 min <sup>-1</sup>
Operating noise	83 dB(A)
Compressed air connection	1/4 in
Connection thread	BSP