

Garant
GARANT Master Tap SteelHT machine tap HSS-E-PM Form B 6GX, TiCN, M: M20

Order data

Order number	131946 M20
GTIN	4062406236342
Item class	111

Description
Version:

High-performance tap, specially developed for use in **steels with high tensile strength** and for **difficult-to-machine materials**. **Strong spiral point**, for process stability at high cutting forces.

- **HSS-E-PM tool material – for very high cutting edge stability.**
- **Optimised honed cutting edges.**
- **TiCN coating – for maximum wear protection.**

Tolerance class: ISO 3X/6GX.

Application:

For components which are galvanised or shrink slightly when hardened.

Recommendation:

For **TOOLOX** and **HARDOX** materials we recommend deviating from the **DIN data** (see table) by **selecting a larger tapping hole \varnothing** .

Technical description

Standard	DIN 376
Thread size	M20
Number of clamping slots	4
Thread depth	60 mm
Overall length L	140 mm
Tapping hole \varnothing	17.5 mm
Tool material	HSS E PM

Thread type	M
Number of cutting edges Z	4
Shank square □	12 mm
Thread pitch	2.5 mm
Thread Ø	20 mm
Tolerance class	ISO 3X 6GX
Shank Ø D _s	16 mm
Coating	TiCN
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	red
Series	Master Tap
Type of product	Tap

User data

	Suitability	V _c	ISO code
Steel < 750 N/mm ²	suitable only under restricted conditions	30 m/min	P
Steel < 900 N/mm ²	suitable	20 m/min	P
Steel < 1100 N/mm ²	suitable	15 m/min	P
Steel < 1400 N/mm ²	suitable		
Steel < 50 HRC	suitable only under restricted conditions		

TOOLOX 33	suitable	15 m/min	H
TOOLOX 44	suitable		
INOX > 900 N/mm ²	suitable		
Ti > 850 N/mm ²	suitable only under restricted conditions		
Oil	suitable		
wet maximum	suitable		