

Garant
Stub drill HSS-E, TiAlN, Ø DC h8: 2,5mm

Order data

Order number	113265 2,5
GTIN	4062406234126
Item class	11B

Description
Version:

High concentricity and **special chip flutes** ensure precise bores.

With point geometry shape C from size 2.4 mm.

Advantage:

Ideal for drilling shallow holes (approx. 2 - 4×D) on NC machines and automatic machines.

Recommendation:
Maximum drilling depth:

$$L_2 = L_c - 1.5 \times D_c.$$

Technical description

Number of cutting edges Z	2
Shank Ø D _s	2.5 mm
Standard	DIN 1897
Nominal Ø D _c	2.5 mm
Flute length L _c	14 mm
Tolerance nominal Ø	h8
recommended maximum drilling depth L ₂	10.3 mm
Point angle	118 degrees
Overall length L	43 mm
Feed f in stainless steel < 900 N/mm ²	0.02 mm/rev.
Shank	Plain shank

Coating	TiAlN
Tool material	HSS E
Through-coolant	no
Colour ring	green
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Alu plastics	Suitable only under restricted conditions	75 m/min	N
Aluminium (short chipping)	Suitable only under restricted conditions	65 m/min	N
Alu > 10% Si	Suitable only under restricted conditions	60 m/min	N
Steel < 500 N/mm ²	suitable	50 m/min	P
Steel < 750 N/mm ²	suitable	40 m/min	P
Steel < 900 N/mm ²	suitable	35 m/min	P
Steel < 1100 N/mm ²	suitable	16 m/min	P
INOX < 900 N/mm ²	suitable	17 m/min	M
INOX > 900 N/mm ²	Suitable only under restricted conditions	13 m/min	M
Ti > 850 N/mm ²	Suitable only under restricted conditions	8 m/min	S
GG(G)	suitable	40 m/min	K
CuZn	suitable	50 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		