

Garant

GARANT Master Tap SteelHT machine tap HSS-E-PM Form B 6HX, TiCN, MF: 10X1



Order data

Order number	132855 10X1
GTIN	4062406236571
Item class	111

Description

Version:

High-performance tap, specially developed for use in **steels with high tensile strength** and for **difficult-to-machine materials. Strong spiral point**, for process stability at high cutting forces.

- **HSS-E-PM tool material – for very high cutting edge stability.**
- **Optimised honed cutting edges.**
- **TiCN coating – for maximum wear protection.**

Recommendation:

For **TOOLOX and HARDOX materials we recommend deviating from the DIN data** (see table) **by selecting a larger tapping hole \varnothing .**

Thread type: MF

Tool material: HSS E PM

Standard: DIN 374

Tolerance class: ISO 2X 6HX

Thread pitch: 1 mm

Overall length L: 90 mm

Shank $\varnothing D_s$: 7 mm

Shank square \square : 5.5 mm

Tapping hole \varnothing : 9 mm

Technical description

Shank $\varnothing D_s$	7 mm
Standard	DIN 374
Tolerance class	ISO 2X 6HX

Tool material	HSS E PM
Number of cutting edges Z	3
Thread depth	30 mm
Overall length L	90 mm
Tapping hole Ø	9 mm
Shank square □	5.5 mm
Thread type	MF
Number of clamping slots	3
Thread pitch	1 mm
Thread Ø	10 mm
Coating	TiCN
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Series	Master Tap
Type of product	Tap

User data

	Suitability	V _c	ISO code
Steel < 750 N/mm ²	Suitable only under restricted conditions	30 m/min	P
Steel < 900 N/mm ²	suitable	20 m/min	P
Steel < 1100 N/mm ²	suitable	15 m/min	P
Steel < 1400 N/mm ²	suitable	12 m/min	P

Steel < 50 HRC	Suitable only under restricted conditions		
TOOLOX 33	suitable	15 m/min	H
TOOLOX 44	suitable		
HARDOX 500 < 1600 N/mm ²	suitable only under restricted conditions		
INOX > 900 N/mm ²	suitable		
Ti > 850 N/mm ²	suitable only under restricted conditions		
Oil	suitable		
wet maximum	suitable		