

Garant
Stub drill HSS-E, TiAlN, Ø DC h8: 9,9mm

Order data

Order number	113265 9,9
GTIN	4062406235604
Item class	11B

Description
Version:

High concentricity and **special chip flutes** ensure precise bores.

With point geometry shape C from size 2.4 mm.

Advantage:

Ideal for drilling shallow holes (approx. 2 - 4×D) on NC machines and automatic machines.

Recommendation:
Maximum drilling depth:

$$L_2 = L_c - 1.5 \times D_c.$$

Technical description

Flute length L_c	43 mm
Shank $\varnothing D_s$	9.9 mm
Overall length L	89 mm
recommended maximum drilling depth L_2	28.2 mm
Standard	DIN 1897
Number of cutting edges Z	2
Nominal $\varnothing D_c$	9.9 mm
Point angle	118 degrees
Tolerance nominal \varnothing	h8
Feed f in stainless steel $< 900 \text{ N/mm}^2$	0.09 mm/rev.
Shank	Plain shank

Coating	TiAlN
Tool material	HSS E
Through-coolant	no
Colour ring	green
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Alu plastics	Suitable only under restricted conditions	75 m/min	N
Aluminium (short chipping)	Suitable only under restricted conditions	65 m/min	N
Alu > 10% Si	Suitable only under restricted conditions	60 m/min	N
Steel < 500 N/mm ²	suitable	50 m/min	P
Steel < 750 N/mm ²	suitable	40 m/min	P
Steel < 900 N/mm ²	suitable	35 m/min	P
Steel < 1100 N/mm ²	suitable	16 m/min	P
INOX < 900 N/mm ²	suitable	17 m/min	M
INOX > 900 N/mm ²	Suitable only under restricted conditions	13 m/min	M
Ti > 850 N/mm ²	Suitable only under restricted conditions	8 m/min	S
GG(G)	suitable	40 m/min	K
CuZn	suitable	50 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		