



## External micrometer with disc anvils and non-rotating spindle, Measuring range: 75-100mm



### Order data

Order number	423005 75-100
GTIN	4062406237783
Item class	42B

### Description

#### Version:

With large-area, hardened disc anvils. Forged and enamelled frame. Design with non-rotating spindle.

#### Application:

For determining the tooth widths of spur and helical gears from module 0.8.

#### Supplied with:

From size 25-50 including 1 setting standard.

### Technical description

Scale divisions	0.01 mm
Disc anvil $\varnothing$	19.5 mm
Calibration	B2
Calibration	B1
Calibration	B2
Micrometer barrel graduations	1/50 mm
Measuring range	75 - 100 mm
Spindle pitch	0.5 mm
Parallelism of the measuring faces	5 $\mu$ m

Spindle Ø	8 mm
Standard	DIN 863
Measurement technology	analogue
Packaging	sturdy box
Type of product	External micrometer

### Services

DAkkS calibration External micrometer including setting dimension maximum measuring range 100 mm	022050 100
Calibration External micrometer including setting dimension maximum measuring range 100 mm	022040 100

### Accessories

Micrometer setting standard overall length 75 mm	421100 75
--	-----------