

FLEX**Polishing machine, Type: XCE10-8125****Order data**

Order number	077771 XCE10-8125
GTIN	4030293180550
Item class	03S

Description**Version:**

- **8 mm positive-action polishing stroke for high abrasive power.**
- **High level of smooth running due to counterweight.**
- **Ideally suited to working on temperature-sensitive paint finishes, thanks to low heat generation on the surface.**
- **Cushioned special hook and loop pad for polishing.**
- **Flat gear head reduces the distance to the surface. This allows the machine to be securely guided in any position.**
- **Grip handle: ergonomically shaped with SoftGrip.**
- **Microprocessor electronics with constant speed control by tacho-generator, soft start, accelerator switch, restart inhibit after a power failure, overload protection, temperature monitoring and speed pre-set.**
- **Optimised air circulation for the best possible cooling of the motor and gear. No irritating exhaust air for the user.**

Technical description

Power consumption	1010 W
Weight	2.6 kg
Manufacturer's designation	XCE 10-8 125
Cable length	4 m

Speed range	140 - 430 min ⁻¹
maximum polishing tool Ø	160 mm
Power supply	Mains operated
Type of product	Polishing machine