



External micrometer with disc anvils and non-rotating spindle, Measuring range: 25-50mm



Order data

Order number	423005 25-50
GTIN	4062406237769
Item class	42B

Description

Version:

With large-area, hardened disc anvils. Forged and enamelled frame. Design with non-rotating spindle.

Application:

For determining the tooth widths of spur and helical gears from module 0.8.

Supplied with:

From size 25-50 including 1 setting standard.

Technical description

Parallelism of the measuring faces	5 μ m
Micrometer barrel graduations	1/50 mm
Calibration	B2
Calibration	B1
Calibration	B2
Disc anvil \varnothing	19.5 mm
Scale divisions	0.01 mm
Spindle \varnothing	8 mm
Measuring range	25 - 50 mm

Spindle pitch	0.5 mm
Standard	DIN 863
Measurement technology	analogue
Packaging	sturdy box
Type of product	External micrometer

Services

Calibration External micrometer including setting dimension maximum measuring range 100 mm	022040 100
DAkkS calibration External micrometer including setting dimension maximum measuring range 100 mm	022050 100

Accessories

Micrometer setting standard overall length 25 mm	421100 25
--	-----------