

Garant
GARANT Master Tap SteelHT machine tap HSS-E-PM Form C 6HX, TiAlN, MF: 3X0,35

Order data

Order number	136350 3X0,35
GTIN	4062406236090
Item class	111

Description
Version:

High-performance tap, specially developed for use in **steels with high tensile strength** and for **difficult-to-machine materials**. Sturdy design with **optimised guide thread to avoid chips jamming**.

- **HSS-E-PM tool material – for very high cutting edge stability.**
- **Optimised honed cutting edges.**
- **TiAlN coating – for maximum wear protection.**

Recommendation:

For **TOOLOX materials** we recommend deviating from the **DIN data** (see table) **by selecting a larger tapping hole \varnothing** .

Note:

For **TOOLOX materials**: do not exceed the maximum thread depth of $2 \times D$!

Technical description

Overall length L	56 mm
Tapping hole \varnothing	2.65 mm
Shank $\varnothing D_s$	2.2 mm
Thread type	MF
Thread depth	7.5 mm
Number of clamping slots	3
Tolerance class	ISO 2X 6HX
Number of cutting edges Z	3

Thread pitch	0.35 mm
Standard	DIN 374
Thread size	M3×0.35
Tool material	HSS E PM
Thread Ø	3 mm
Coating	TiAlN
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	C
Helix angle	40 degrees
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	red
Series	Master Tap
Type of product	Tap

User data

	Suitability	V _c	ISO code
Steel < 750 N/mm ²	suitable only under restricted conditions	30 m/min	P
Steel < 900 N/mm ²	suitable	20 m/min	P
Steel < 1100 N/mm ²	suitable	15 m/min	P
Steel < 1400 N/mm ²	suitable		
Steel < 50 HRC	Suitable only under restricted conditions		
TOOLOX 33	suitable	15 m/min	H

TOOLOX 44	suitable
INOX > 900 N/mm ²	suitable
Ti > 850 N/mm ²	Suitable only under restricted conditions
Oil	suitable
wet maximum	suitable