

Garant**LED cordless work light, Type: 500****Order data**

Order number	081442 500
GTIN	4062406236113
Item class	01A

Description**Version:**

Versatile LED cordless work lamp in slim sturdy design with a wide range of applications. Practical monitoring of the state of charge of the battery by LED display directly on the lamp.

- **Main lamp steplessly dimmable from 10 - 100 %.**
- **Integral spotlight function.**
- **Flexible use thanks to 180° pivoting magnetic base, together with fold-up and rotating suspension hook.**

Charging station compatible with the GARANT easyFix system. Uncomplicated charging, ready to hand at all times.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Supplied with USB-C charging cable and plug-in power supply unit.

Note:

For mounting on Easyfix perforated panels, order the Easyfix plastic base plate No. 955820 size 2 also.

Technical description

IP Index of Protection	IP 65
Bulb	LED module
Number of rechargeable batteries contained	1
Type of rechargeable battery	Lithium-ion
Overall width	47 mm
Battery voltage	3.7 V
Illumination	50 - 500 lm
Illumination time	2 - 20 h
Battery capacity	3 Ah
Weight	257 g
Power supply	Rechargeable battery-powered
Overall length	230 mm
ATEX zone	no
Type of product	Work lamp

Accessories

USB charger Type CABLE	081432 CABLE
Li-ion battery Battery capacity 3000 mAh	081431 3000
USB charger Type CHARGER	081432 CHARGER
Cordless lamp spare parts Type 2	081434 2
Charging station Easy Fix Type 500	081453 500