



External micrometer with disc anvils and non-rotating spindle, Measuring range: 0-25mm



Order data

Order number	423005 0-25
GTIN	4062406237752
Item class	42B

Description

Version:

With large-area, hardened disc anvils. Forged and enamelled frame. Design with non-rotating spindle.

Application:

For determining the tooth widths of spur and helical gears from module 0.8.

Supplied with:

From size 25-50 including 1 setting standard.

Technical description

Disc anvil \varnothing	19.5 mm
Micrometer barrel graduations	1/50 mm
Scale divisions	0.01 mm
Calibration	B1
Spindle \varnothing	8 mm
Measuring range	0 - 25 mm
Parallelism of the measuring faces	5 μ m
Spindle pitch	0.5 mm
Standard	DIN 863

Measurement technology	analogue
Packaging	sturdy box
Type of product	External micrometer

Services

Calibration External micrometer without setting dimension maximum measuring range 25 mm	022000 25
DAkkS calibration External micrometer without setting dimension maximum measuring range 100 mm	022010 100