

## Garant

**Milling head arbor Form ADB with cooling channel bores, SK 40 A = 200,  
Spigot Ø d1: 32 mm**



### Order data

Order number	301075 32
GTIN	4062406242121
Item class	31A

### Description

#### Version:

- From clamping Ø 40 with 4 tapped holes for face mills to DIN 2079.
- Taper shank, spigot, and all contact surfaces ground at the collar.
- Short series.
- Increased collar contact surface.
- With Balluffchip bore.
- With 4 cooling channel bores.
- All shanks hard turned (for smooth running!).

#### Supplied with:

Lock screw.

#### Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835, Special toggle spanner No. 309840. Milling cutter lock screws No. 309860; 309861.

External Ø D: 78 mm

Milling mandrel length L<sub>4</sub>: 24 mm

Spare milling cutter lock screw No. 309860 / 309861: 32

Suitable toggle spanner No. 309840: 32

### Technical description

External Ø D	78 mm
Milling mandrel length L <sub>4</sub>	24 mm

Spare milling cutter lock screw No. 309860 / 309861	32
Suitable toggle spanner No. 309840	32
Spigot $\varnothing d_1$	32 mm
Adapter	SK 40 A = 200
Standard	DIN 6357
Arbor standard	ISO 7388-1
Shape	ADB
Cooling channel bore	not pluggable
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 5 \mu\text{m}$
Machining strategy	HPC
Type of product	Milling head arbor