

## Garant

**Face mill arbor Form ADB with cooling channel bore, SK 50 A = 200, Spigot Ø d1: 32mm**



### Order data

Order number	301154 32
GTIN	4062406242169
Item class	31A

### Description

#### Version:

- Taper shank, spigot, and all contact surfaces are ground at the collar.
- Short series.
- Increased collar contact surface.
- With RFID/Balluffchip bore.
- With 4 cooling channel bores.
- All shanks hard turned (for smooth running!).

#### Supplied with:

Lock screw.

#### Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835, Special toggle spanner No. 309840. Milling cutter lock screws No. 309860; 309861.

### Technical description

Suitable toggle spanner No. 309840	32
Overhang dimension A	200 mm
Spigot Ø d <sub>1</sub>	32 mm
Milling mandrel length L <sub>4</sub>	24 mm
Spare milling cutter lock screw No. 309860 / 309861	32

External Ø D	78 mm
Clamping Ø D <sub>1</sub>	32 mm
Adapter	SK 50 A = 200
Standard	DIN 6357
Arbor standard	ISO 7388-1
Shape	ADB
Cooling channel bore	not pluggable
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 5 µm
Machining strategy	HPC
Type of product	Milling head arbor