

**Welder's clamp, overall length: 275mm****Order data**

Order number	709201 275
GTIN	4062406241049
Item class	72B

Description**Version:**

U-shaped clamping jaws; upper jaw angled 90°. Sturdy spring steel body. Fully nickel-plated.

Application:

For clamping profiled or flat materials etc. when welding.

Material:

Chrome vanadium steel clamping jaws.

Spare part:

Spare spring No. 708301 size 10.

Technical description

Jaw capacity a	55 mm
overall length	275 mm
upper gripper jaw	90° angled
Type of jaws	U-shape
Material of pliers	Spring steel
Material of gripper jaws	Chrome vanadium steel
Surface	nickel-plated
Type of product	Grip wrench

Accessories

Spring Type 10

708301 10