

Garant
Face mill arbor with cooling channel bores, PSC 40 short, Spigot \varnothing d1: 16mm

Order data

| | |
|--------------|---------------|
| Order number | 308543 16 |
| GTIN | 4062406243807 |
| Item class | 31C |

Description
Version:

- With RFID/Balluffchip bore.
- All shanks hard turned (for smooth running!).
- Mating faces of the PSC internal contour machined.

Application:

For holding shell end mills and face mills with cross keyway.

Supplied with:

Lock screw.

Optional extras:

Toggle spanner No. 309840, cutter lock screw No. 309860.

Coolant tube and assembling key for coolant tubes No. 309885; 309893.

Technical description

| | |
|---|-------|
| Spare milling cutter lock screw No. 309860 / 309861 | 16 |
| External \varnothing D | 38 mm |
| Suitable toggle spanner No. 309840 | 16 |
| Overhang dimension A | 32 mm |
| Spigot \varnothing d ₁ | 16 mm |
| Clamping \varnothing D ₁ | 16 mm |

| | |
|---------------------------------------|---------------------|
| Adapter | PSC 40 short |
| Arbor standard | ISO 26623-1 |
| Cooling channel bore | pluggable |
| Balance quality G at rotational speed | G 2.5 at 25,000 rpm |
| Concentricity | ≤ 6 μm |
| Machining strategy | HPC |
| Type of product | Milling head arbor |

Accessories

| | |
|------------------------------------|-----------|
| Toggle spanner for mandrel Ø 16 mm | 309840 16 |
|------------------------------------|-----------|