

Garant**ER hydraulic collet with clamping nut ER32, Ød: 20mm****Order data**

Order number	319743 20
GTIN	4062406244064
Item class	31W

Description**Version:**

High flexibility for use with turning in static collet holders, but also when using driven tools. Best run-out characteristics.

For driven tools with external threads.

Advantage:

- **Ideal damping characteristics, resulting in optimum component surfaces and increased tool life.**
- **Quick and easy handling.**
- **Flexible use of reducing adapters.**
- **Perfect centring.**

Application:

Suitable for drilling, reaming, countersinking and also for use of boring bars.

Technical description

Ø d	20 mm
Thread M	M40×1.5
Ø d ₂	50 mm
Length L	58.3 mm

Type of product

Collet